


CUSTOMER NAME				OB NO.	ITEM NO.	Design Confirmation		APPROVED BY	CHECKED BY	PERSON IN CHARGE
Matsui Technologies India Limited				OB000000000				MATSUMOTO	VIKAS	VIVEK
HISTRY				AP:						
				PIC:						
				AP:						
				PIC:						
				AP:						
				PIC:						
						STANDARD		DELIVERY TIME	INSTRUCTION MANUAL	
PAINTING	M	1. AN-80	2. SPECIFICATION ATTACHED	3. COLOR NO.				FINISH AND DRAWING STANDARD		
	E	1. AN-80	2. SPECIFICATION ATTACHED	3. COLOR NO.	OUTER	INNER				
										UNLESS OTHERWISE SPECIFIED IN THE DRAWING, MST-536 MACHINING STANDARD. MST-541 DRAWING REGULATION AND 241-003/503 PRODUCT INSPECTION PROCEDURE (STANDARD) SHALL APPLY. IF THEY ARE INSUFFICIENT, THE JIS STANDARD SHALL APPLY. CONTENT OF VERIFICATION CHECKLIST SHALL APPLY FOR DYNAMIC CHECK.
MODEL CODE			NAME	DEHUMIDIFYING DRYER		Date				
DRAWING NO.		N180707P04		MODEL	MJ3-200					
DESIGNER		M SANDEEP	E VIKAS	APPROVAL MATSUMOTO	POWER-OPERATION-	AC, AC	Hz			
NOTED SPECIFICATION										


DRAWING NO.	SIZE	MODEL CODE	MODEL	NAME, MODEL	LOT	QTY	REMARK	REV
N180707P04	A4		MJ3-200	CONTROL PANEL	1	1	STD	
849755	A4		MJ3-200	CIRCUIT DIAGRAM 1 (POWER-1)	1	1	STD	
849756	A4		MJ3-200	CIRCUIT DIAGRAM 2 (POWER-2)	1	1	STD	
849757	A4		MJ3-200	CIRCUIT DIAGRAM 3 (CONTROLLER)	1	1	STD	
846157	A4		MJ3-10~300	CIRCUIT DIAGRAM 2 (JET SELECTOR)	1	1	STD	
844332	A4		MJ3-10~300	CIRCUIT DIAGRAM 6 (DEW POINT & WEEKLY TIMER)	1	1	STD	
849634	A4		MJ3-200~300	CIRCUIT DIAGRAM 4 (SIGNAL)	1	1	STD	
INA000144	A4		MJ3-10~300	CIRCUIT DIAGRAM 1 (PRE DRYING TIMER)	1	1	STD	



Technical drawing of a rectangular room layout, oriented horizontally. The overall dimensions are 1300 (width) by 213 (height). The layout includes several rectangular blocks representing equipment or furniture, labeled as follows:


- Top-left area:** A large rectangular block labeled "Tr-1". To its right is a smaller block labeled "OP-2-2" with a width of 7.
- Top-right area:** A large rectangular block labeled "OP-4-2" with a width of 105. To its right is a smaller block labeled "OP-3-2" with a width of 10.
- Bottom-left area:** A large rectangular block labeled "SSR-1" with a width of 8. To its right is a smaller block labeled "SSR-2" with a width of 7. Further right is a block labeled "MC-0" with a width of 8. To the right of "MC-0" is a block labeled "SSR-3" with a width of 8. To the right of "SSR-3" is a block labeled "SSR-4" with a width of 8. To the right of "SSR-4" is a block labeled "TB-2" with a width of 7. To the right of "TB-2" is a block labeled "OP-4-2" with a width of 105. To the right of "OP-4-2" is a block labeled "OP-3-2" with a width of 10.
- Bottom-right area:** A large rectangular block labeled "MS-1" with a width of 8. To its right is a block labeled "MS-2" with a width of 8. To the right of "MS-2" is a block labeled "OCR-1" with a width of 8. To the right of "OCR-1" is a block labeled "OCR-2" with a width of 8. To the right of "OCR-2" is a block labeled "OCR-3" with a width of 8. To the right of "OCR-3" is a block labeled "TB-1" with a width of 7. To the right of "TB-1" is a block labeled "OP-4-2" with a width of 105. To the right of "OP-4-2" is a block labeled "OP-3-2" with a width of 10.

Dimensions are indicated by arrows and numbers. The overall width is 1300, and the overall height is 213. The drawing is oriented horizontally, with the 1300 dimension running vertically and the 213 dimension running horizontally.



REVISION		MARK	DATE	CONTENTS	CHKD	APPD
△						
△						
△						
△						

NAME					M/J-200J		FORM		CONTROL PANEL	
APPROVED BY					MATSUMOTO		CODE NO.		...	
DSGND (CHKD) BY					VIKAS		DATE		JULY/07/2018	
DRAWN BY					NISHA		UNIT mm		PLANE TRIANGOMETRY	
SCALE					1:6		DWG. NO.		N180707P04	
MATSUI TECHNOLOGIES INDIA LIMITED										



REVISION	5	AUG./24/2016	K. TSUJII	M. NAKANO	A. ITOI	SCALE	CODE NO.		
	4	JUN/13/2008	Change 3-direction select valve	TSUJII	OKUDA	APPROVED BY	YAMAMOTO	FORM	CIRCUIT DIAGRAM (3)
	3	OCT/13/2006	Name Change (STANDBY – CONTROL ON) TSUJII	YOKOTANI	YAMAMOTO	DSGND (CHKD) BY	YOKOTANI	DATE	NOV/1/2002
	2	APR/22/2005	Air selector valve changed to normal No. 1	YAMAMOTO	YAMAMOTO	UNIT	mm	PLANE	TRIGONOMETRY
	MARK	DATE	CONTENTS	CHKD	APPD	DRAWN BY	•		
MATSUI TECHNOLOGIES INDIA LIMITED									
			NAME		MJ3-200J		DWG. NO.		849757

ITEM NO.	DESCRIPTION	REQ. D	MATERIAL	REFERENCE

03-

00

01

02

03

04

05

06

07

08

09

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

25

26


27

28

29

30


31




--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

NO. 1 DIRECTION NO. 1


LIMIT SWITCH CONTROL TYPE




LEVEL SWITCH CONTROL TYPE



PROXIMITY SWITCH CONTROL TYPE




PHOTOTUBE CONTROL TYPE




Standard dwg.

NO. 2 DIRECTION NO. 2


LIMIT SWITCH CONTROL TYPE




LEVEL SWITCH CONTROL TYPE



PROXIMITY SWITCH CONTROL TYPE




PHOTOTUBE CONTROL TYPE




NO. 3 DIRECTION NO. 3


LIMIT SWITCH CONTROL TYPE




LEVEL SWITCH CONTROL TYPE



PROXIMITY SWITCH CONTROL TYPE




PHOTOTUBE CONTROL TYPE



		849634		Matsui Technology India Limited	
		DWG. NO.			
		MJ3-200~300			
		NAME			
		CIRCUIT DIAGRAM (4)			
		FORM			
		DATE			
		UNIT mm			
		CODE NO.			
		YAMAMOTO			
		YOKOTANI			
		-			
		APPROVED BY			
		DSGND (CHKD) BY			
		DRAWN BY			
		SCALE			
		APPD			
		CHKO			
		NO. 845265			
		CONTENTS			
		DATE			
		MARK			
		REVISION			

A B C D



NAME		PRE DRYING TIMER		DWG. NO.		INA000144	
Matsui Technologies India Limited							
CIRCUIT DIAGRAM 1		FORM		DATE		NOV/22/2017	
SCALE		Not		APPROVED BY		DSGND (CHKD) BY	
CODE NO.		NISHI		VIKAS		VIKAS	
UNIT mm		DATE		VIKAS		VIKAS	
DRAWN BY		APPD		CHKD		CONTENTS	
DATE		MARK		REVISION			